


## Catalog Number

95025-08-2S

**Caps, Headspace, Crimp Top, with White Silicone Rubber / Natural Transparent PTFE, High Purity Septa, fitted in Aluminum, Silver Pressure Relief Caps with 8mm center holes. For use with 20mm Crimp Top**



### Additional Info

High Purity Silicone Rubber / PTFE Septa with Durometer of 45 Shore A, (hardness) and 3.0mm thick with Ultra Low Bleed Rubber that is made with a proprietary process for ultra durability, purity and low extractables.

Excellent choice for highly sensitive analyses. The lower Durometer means that this is a softer Septa and therefore better for easier penetrations by autosampler needles.

Wide temperature range from -60° to 200°C. Clear lacquered Caps have score lines that will break open at 3.0 +/- 0.5 Bar, for safety.

### MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: [customers@mtc-usa.com](mailto:customers@mtc-usa.com)

Website: [www.mtc-usa.com](http://www.mtc-usa.com)

### Price

**\$69.43**

Printed On 2024/05/20