


## Catalog Number

95025-23

**Septa, 20mm, Headspace, White Silicone Rubber / Blue PTFE Foil.** For use in 20mm Crimp Caps, sold separately. BASIK Brand. 1000/CS.



### Additional Info

Silicone Rubber / PTFE Septa with Durometer of 50 Shore A, (hardness) and 3.0mm thick is good for higher temperature analyses.

Temperature range from -60° to 200°C.

Use in Aluminum or Steel Crimp Caps for Headspace autosamplers. *Supplied in Polyethylene Bags.*

### MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: [customers@mtc-usa.com](mailto:customers@mtc-usa.com)

Website: [www.mtc-usa.com](http://www.mtc-usa.com)

### Price

**\$483.73**

Printed On 2024/05/20