

Catalog Number

9582S-30C-K-M

Caps, Screw Top, with 1.3mm thick Silicone Rubber / PTFE Pre-Slit Septa, fitted in "knurled", polypropylene, Black Caps with 5.5mm center holes. For use with 8-425mm thread, 12x32mm autosampler vials.



Additional Info

Pre-Slit for easy penetration by autosampler needles.

Click [HERE](#) for smaller pack quantities.

MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: customers@mtc-usa.com

Website: www.mtc-usa.com

Price

\$683.91

Printed On 2024/05/20