


## Catalog Number

97041-09

**Septa, 22mm, Translucent Silicone Rubber / Natural PTFE. Ultra Low Bleed. For use in 24mm Caps, sold separately. BASIK Brand. 1000/CS.**



### Additional Info

Silicone Rubber / PTFE Septa 2.5mm thick. This Septa is good for storage or EPA Testing due to the high purity of the rubber and PTFE. Temperature range from -60° to 200°C.

Use in screw caps that have 24mm or ND2 threads.. Supplied in a polyethylene Bags.

### MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: [customers@mtc-usa.com](mailto:customers@mtc-usa.com)

Website: [www.mtc-usa.com](http://www.mtc-usa.com)

### Price

**\$869.94**

Printed On 2024/05/19