

Catalog Number

48220-02-002

Mobile Phase Filter, 2 μ m, Stainless Steel, 0.375 inch OD, 1 inch long, 1/8 inch connector. EPP-Porous Products brand. 2/PK.



Additional Info

These Economical 316L stainless steel filters are designed for use with 1/8-inch tubing and feature PEEK tubing connectors. They are manufactured to provide high filtering capacity and excellent mobile phase solvent throughput. Passivated with a 30% nitric acid solution, the 2 μ m porosity effectively filters out larger, undissolved particles from your mobile phases or solvents, preventing them from entering your HPLC pumps, columns, and instruments, thereby reducing potential damage.

Simple to install:

Price
\$99.98

Additional Info

- Insert the tubing into the hole at the top of the filter and tighten it by hand.
- Place the assembled filter at the bottom of your mobile phase reservoir bottle.
- Connect the tubing to the inlet of your HPLC pump.

Included with each *Mobile Phase Solvent Filter* is one ETFE ferrule and one low pressure male nut connector for use with 1/8th inch (3.2 mm) OD tubing. Tubing sold separately. For sparging, you can also connect the filter to a low-pressure helium or nitrogen line.

- Click [HERE](#) for replacement ferrules.
- Click [HERE](#) for economical pack of 5 filters.

MicroSolv

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: customers@mtc-usa.com

Website: www.mtc-usa.com

Price

\$99.98