

Catalog Number

58522-N47

Filters, Membrane, 47mm, 0.22um, Nylon. Round, AQ Brand. 100/PK.



Additional Info

These high flow, non media migrating, Nylon-66, Advanced Quality (AQ) Brand, Filter Discs can be used with the Mobile Phase Filter Degasser Assembly or any device when membrane filtration is desired.

Hydrophilic membranes with minimal extractables and absolute retention, they can be autoclaved at 121 °C for 30 minutes or EO sterilization without damage to the integrity or performance of the filter.

- Diameter: 47mm

Price
\$176.98

Additional Info

- Max Operating Temperature: 80 °C
- Bubble Point: >50psi (3.52 kg/cm²)
- Water Flow Rate: >12ml/min/cm² @ 10 psi, 27 °C
- Thickness: 150um +- 20um
- Extractables with WFI (water): Within USP Limits
- Oxidizable Substances: Passes USP Test
- Pore Size: 0.22 um
- HPLC Certified for Reliability & Accuracy

Click [Here](#) for 0.45um Nylon.

MicroSolv

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: customers@mtc-usa.com

Website: www.mtc-usa.com

Price

\$176.98