

## Catalog Number

68112-10P-2

**UHPLC Column, RP C12, 1.8 $\mu$ m, 100A. 2.1mm ID x 100mm Length.**

Cogent Brand. 1 EA.

**MOST POPULAR**



### Additional Info

This Cogent RP C12™ UHPLC Stationary Phase and Column has been a premium value and used by HPLC laboratories for several years. It is double end capped (*fully*), and bonded with a rigid Adamantine shaped (diamond like) carbon silane to the highest purity silica available; making this column excellent for high throughput screening (HTS) with rapid equilibration between runs.

The small, 1.8 $\mu$ m Particle Size will provide high efficiency even at high flow rates with greater Peak Capacity than other typical Particle Sizes but higher back pressures are normal and to be expected. This column is compatible with any Reversed Phase mobile phase including 100% water without any loss of retention run to run, which is why this column is often used for high throughput methods that separate complex mixtures. Normally, you can expect less retention than a C18 column but more than a C8 column for the same hydrophobic compounds. This is one of our Most Popular C12 HPLC Columns and it is often used with LCMS.

### MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: [customers@mtc-usa.com](mailto:customers@mtc-usa.com)

Website: [www.mtc-usa.com](http://www.mtc-usa.com)

### Price

**\$1,466.33**

Printed On 2024/05/08