


Catalog Number

95025-23

Septa, 20mm, Headspace, White Silicone Rubber / Blue PTFE Foil. For use in 20mm Crimp Caps, sold separately. BASIK Brand. 1000/CS.



Additional Info

Silicone Rubber / PTFE Septa with Durometer of 50 Shore A, (hardness) and 3.0mm thick is good for higher temperature analyses.

Temperature range from -60° to 200°C.

Use in Aluminum or Steel Crimp Caps for Headspace autosamplers. *Supplied in Polyethylene Bags.*

MicroSolv Technology Corporation

9158 Industrial Blvd. NE, Leland, NC 28451

tel. (732) 380-8900, fax (910) 769-9435

Email: customers@mtc-usa.com

Website: www.mtc-usa.com

Price

\$483.73

Printed On 2024/05/04